


pH measurements: How to see the real face of electrochemistry and corrosion?

December 18 2012



Antimony microelectrodes for pH measurement at metal surfaces, developed at the Institute of Physical Chemistry of the Polish Academy of Sciences in Warsaw, will assist in a better understanding of the nature of electrochemical and corrosion processes. The picture shows Dr. Iwona Flis-Kabulska. Credit: Institute of Physical Chemistry, Polish Academy of Sciences

For several decades antimony electrodes have been used to measure the acidity/basicity – and so to determine the pH value. Unfortunately, they allow for measuring pH changes of solutions only at a certain distance from electrodes or corroding metals. Researchers at the Institute of Physical Chemistry of the Polish Academy of Sciences developed a method for producing antimony microelectrodes that allow for measuring pH changes just over the metal surface, at which chemical reactions take place.

Changes in solution acidity/basicity provide important information on the nature of [chemical reactions](#) occurring at metal surfaces. These data are particularly important for a better understanding of electrochemical and corrosion processes. Unfortunately, the measurement methods used to date in the research laboratories did not allow for observing the changes with sufficient precision.

The information on basicity or acidity is contained in the well-known and commonly used [pH value](#). pH for pure (inert) water is equal to 7, for hydrochloric acid – 0, and for [sodium hydroxide](#) (one of the strongest bases) – 14.

"Until now we have not been able to measure pH changes at places where the most interesting things occur: at the very metal surface. The [measurements](#) had to be carried out at a certain distance, in the electrolyte bulk, as we call it. It's obvious that the data collected under such circumstances not always accurately and not always immediately reflected what was really going on at the metal surface", says Dr Iwona Flis-Kabulska from the Institute of [Physical Chemistry](#) of the Polish Academy of Sciences (IPC PAS) in Warsaw.

In an attempt to better understand the mechanisms governing the [electrochemistry](#) and corrosion of metal surfaces, researchers from the IPC PAS developed a new [measurement tool](#). It is an antimony [microelectrode](#) with a design allowing for performing easy and reproducible measurements just over the metal surface – at a distance of one tenth of a millimeter only. A patent application for the device was filed.

The new microelectrode is made of a glass capillary filled with liquid antimony. Stretched to reduce the cross section and cut flat, the microelectrode enables carrying out measurements at hard surfaces, in a liquid environment. It is thus suitable for monitoring electrochemical

reactions and corrosion processes resulting from interaction between metal and solution or a thin water film.

A good point of the microelectrode developed at the IPC PAS is that the measurements can be easily performed. The designs available earlier on the market required, i.a., the use of micromanipulators for precise placement of [electrodes](#) at the surface. "We make use of ordinary geometry. We just move a flat cut glass microelectrode tip closer to the surface of the tested metal, at an appropriate angle. We know the tip diameter and the angle, at which it has been moved closer to the surface, so we know immediately how it is tilted to the surface, and therefore what is the distance between the metal and the antimony core inside the electrode", says Dr Flis-Kabulska.

During measurements, the flat microelectrode tip is tilted to the surface of the tested metal, which means that it does not contact the [metal surface](#) with its entire surface. This fact provides additional benefits. Protons produced in reactions on the surface do not disperse quickly in the solution. Their diffusion is slowed down, and it significantly increases the instrument sensitivity and the accuracy of measurements.

The antimony microelectrode from the IPC PAS shows the highest sensitivity in measurements of pH changes ranging from 3 to 10.

The application potential of the new microelectrode is broad. The instrument was constructed with applications in the laboratory research in mind. Due to low manufacturing cost, simplicity and reproducibility of measurements, as well as high sensitivity to changes, the microelectrode could be also used in field tests, for instance as a component of sensors monitoring the condition of reinforced concrete structures.

Provided by Institute of Physical Chemistry of the Polish Academy of Sciences

Citation: pH measurements: How to see the real face of electrochemistry and corrosion? (2012, December 18) retrieved 25 April 2024 from <https://phys.org/news/2012-12-ph-real-electrochemistry-corrosion.html>

This document is subject to copyright. Apart from any fair dealing for the purpose of private study or research, no part may be reproduced without the written permission. The content is provided for information purposes only.