


Creation of the most perfect graphene

August 25 2021



(a, b) SEM images and (c) AFM phase image of graphene folds in an adlayerfree single-crystal graphene film on a Cu(111) foil. (d) Schematic of the mechanism of graphene folds formation during the cooling process. Credit: Institute for Basic Science




A team of researchers led by Director Rod Ruoff at the Center for Multidimensional Carbon Materials (CMCM) within the Institute for Basic Science (IBS), including graduate students at the Ulsan National Institute of Science and Technology (UNIST), have achieved growth and characterization of large area, single-crystal graphene that has no wrinkles, folds, or adlayers. It may be the most perfect graphene that has been grown and characterized to date. The research has been published in the journal *Nature*.

Director Ruoff says, "This pioneering breakthrough was due to many contributing factors, including human ingenuity and the ability of the CMCM researchers to reproducibly make large-area single-crystal Cu-Ni(111) foils, on which the graphene was grown by chemical vapor deposition (CVD) using a mixture of ethylene with hydrogen in a stream of argon gas." Student Meihui Wang, Dr. Ming Huang, and Dr. Da Luo along with Ruoff undertook a series of experiments of growing single-crystal and single-layer graphene on such "home-made" Cu-Ni(111) foils under different temperatures.

The team had previously reported single-crystal and adlayer-free films of graphene which were grown using methane at temperatures of ~1320 Kelvin (K) degrees on Cu(111) foils. Adlayers refer to small "islands" of regions that have another layer of graphene present. However, these films always contained long "folds" that are the consequence of tall wrinkles that form as the graphene is cooled from the growth temperature down to room temperature. This results in an undesirable reduction in the performance of graphene field effect transistor (GFET) if the "fold" is in the active region of the GFET. The folds also contain "cracks" that lower the mechanical strength of the graphene.

The next exciting challenge was thus eliminating these folds.





(a) Optical image, (b) atomic resolution TEM (transmission electron microscope) image, and (c) representative selected area electron diffraction (SAED) pattern of a fold-free adlayer-free graphene film grown on Cu-Ni(111) foil made by the CMCM. (d) A 6-inch quartz tube CVD furnace system used to evaluate scalable production of single-crystal fold-free graphene films on single-crystal Cu-Ni(111) alloy foils. (e) 5 pieces of 4 cm \times 7 cm Cu-Ni(111) alloy foils were hung on a quartz holder and graphene was grown on both sides of each foil. (f) Photograph of the 4 cm \times 7 cm fold-free single-crystal graphene film grown in the 6-inch CVD system shown in (e) and then transferred onto a 4-inch diameter silicon wafer. Credit: Institute for Basic Science

CMCM researchers first implemented a series of 'cycling' experiments that involved "cycling" the temperature immediately after growing the graphene at 1320 K. These experiments showed that the folds are formed at or above 1,020 K during the cooling process. After learning



this, the team decided to grow graphene on Cu-Ni(111) foils at several different temperatures around 1,020 K, which led to a discovery that large-area, high-quality, fold-free, and adlayer-free single-crystal graphene films can be grown in a temperature range between 1,000 K and 1,030 K. "This fold-free graphene film forms as a single crystal over the entire growth substrate because it shows a single orientation over a large-area *low-energy electron diffraction* (LEED) patterns," noted SEONG Won Kyung, a senior research fellow in CMCM who installed the LEED equipment in the center. GFETs were then patterned on this single-crystal fold-free graphene in a variety of directions by UNIST graduate student Yunqing Li. These GFETs showed remarkably uniform performance with average room temperature electron and hole mobilities of $7.0 \pm 1.0 \times 10^3$ cm² V⁻¹ s⁻¹.

Li says, "Such remarkably uniform performance is possible because the fold-free graphene film is a single crystal with essentially no imperfections."

Importantly, the research team was able to achieve "scaling up" of graphene production using this method. The graphene was successfully grown on 5 foils (dimension 4 cm x 7 cm) simultaneously in a 6-inch diameter home-built quartz furnace. "Our method of growing fold-free graphene films is very reproducible, with each foil yielding two identical pieces of high-quality graphene films on both sides of the foil," and "By using the electrochemical bubbling transfer method, graphene can be delaminated in about one minute and the Cu-Ni(111) foil can be quickly readied for the next growth/transfer cycle," notes Meihui Wang. Ming Huang adds, "When we tested the weight loss of Cu-Ni(111) foils after five runs of growth and transfers, the net loss was only 0.0001 grams. This means that our growth and transfer methods using the Cu-Ni(111) can be performed repeatedly, essentially indefinitely."

In the process of achieving fold-free single-crystal graphene, the



researchers also discovered the reasons behind the formation of these folds. High-resolution TEM imaging was performed by student CHOE Myeonggi and Prof. LEE Zonghoon (a group leader in CMCM and professor at UNIST) to observe the cross-sections of the samples grown above 1,040 K. They discovered that the deadhesion, which is the cause of the folds, is initiated at the "bunched step edge" regions between the single crystal Cu-Ni(111) plateaus. "This deadhesion at the bunched step edge regions triggers the formation of graphene folds perpendicular to the step edge direction," noted co-corresponding author Luo. Ruoff further notes that "We discovered that step-bunching of a Cu-Ni(111) foil surface suddenly occurs at about 1,030 K, and this 'surface reconstruction' is the reason why the critical growth temperature of fold-free graphene is at ~1,030 K or below."

Such large-area fold-free single-crystal graphene film allows for the straightforward fabrication of integrated high-performance devices oriented in any direction over the entire graphene film. These single-crystal graphene films will be important for further advances in <u>basic</u> science, which will lead to new applications in electronic, photonic, mechanical, thermal, and other areas. The near-perfect graphene is also useful for stacking, either with itself and/or with other 2D materials, to further expand the range of likely applications. Given that the Cu-Ni(111) foils can be used repeatedly and that the graphene can be transferred to other substrates in less than one minute, the scalable manufacturing using this process is also highly promising.

More information: Single-crystal, large-area, fold-free monolayer graphene, *Nature*, <u>DOI: 10.1038/s41586-021-03753-3</u>, <u>www.nature.com/articles/s41586-021-03753-3</u>

Provided by Institute for Basic Science



Citation: Creation of the most perfect graphene (2021, August 25) retrieved 17 July 2024 from <u>https://phys.org/news/2021-08-creation-graphene.html</u>

This document is subject to copyright. Apart from any fair dealing for the purpose of private study or research, no part may be reproduced without the written permission. The content is provided for information purposes only.