


# Robot speeds up glass development

November 7 2011

---



A robot arm takes over the fully automatic handling of the test melts in the glass screening unit - here, the pouring of the melt into the sample form. Credit: Knud Dobberke for Fraunhofer ISC

Model by model, the electronics in a car are being moved closer to the engine block. This is why the materials used for the electronics must resist increasing heat – so the glass solder being used as glue must be continually optimized. For the first time ever, a robot takes on the task of developing new types of glass and examining their characteristics. Researchers will introduce this robot at the “productronica“ trade fair to be held in Munich, Germany, from November 15 - 18, 2011.

For laymen glass looks like [glass](#) – it might be a window, a drinking

vessel, a lense for an automotive headlight. But there is much more in and to the transparent material: glass can consist of 50 to 60 different elements. Experts are constantly being asked to create glass with certain characteristics out of these elements, since new applications require new materials quite often. Let's take the car as an example: the electronic components in a car's engine compartment are being brought ever closer to the engine and so must increasingly be resistant to heat and corrosive gasses. This also applies to the glue, a glass solder. In the development of fuel cells, the demand for new types of glass is also great: the use of new metals requires that the glass solder also be adapted. In addition, over a period of approximately 100,000 hours, the glass must withstand thermal heat of 900 degrees Celsius without being damaged.

In order to develop glass with new characteristics, experts select about ten compounds from potential elements, mix them and then heat the powder. They heat it in a furnace until it is soft, then they pour it into a mould and let it cool slowly and in a controlled fashion, down to room temperature. During that process small samples from the viscous glass are taken to test it: how viscous is it? How well does it wet metals? How does it crystallize out? To produce the glass samples by hand and to test them requires a lot of time: one employee needs approximately two weeks to process 16 samples.

Researchers of the Fraunhofer Institute for Silicate Research ISC in Würzburg have developed a unit that carries out all these steps automatically. "It needs only 24 hours to process 16 samples", says Dr. Martin Kilo, manager of the expert group for glass and high-temperature materials at the ISC. "For this reason we are able to develop glass elements more cost-effectively than previously, by up to 50 percent." The core piece of the unit is a robot: it puts a mixing cup on a scale and moves it under 14 storage vessels, from which a certain amount of powder is filled into the cup. Then the robot mixes the individual ingredients by closing the cup and shaking it, just like a bartender does

with a cocktail shaker. The robot arm then grabs a crucible, puts it onto the scale, fills it with a certain amount of the mixed powder and puts the crucible into one of the five furnaces available in total. The robot repeats this steps several times, since gases build up when the powder is heated and foam could form otherwise. In addition, the powder shrinks during the melting process. Finally the furnace heats the fully filled crucible to a higher temperature, causing the gas bubbles in the glass to rise to the surface. Once the glass is viscous, the robot arm removes the crucible, pours the glass into a new mould and places it in a stress-relieving furnace. Here, the glass cools slowly and in a controlled manner, from 600 to 800 degrees Celsius down to room temperature.

An additional central element of the unit is the analysis unit. It works according to the thermo-optical measurement principle. Looking through two measurement windows, the shade the sample projects in a backlight test system is recorded by a CCD camera. The changes in the contour make it possible to determine characteristics such as sample volume, hemisphere point and wetting angle. This test unit measures how viscous the melt is, and if and how it crystallizes and wets metals. The test unit can also be used independently of the glass screening unit. The unit also determines and records the ability of the glass to conduct heat. Researchers will introduce this robot at the "productronica" trade fair that takes place in Munich, Germany, from November 15 -18, 2011.

Provided by Fraunhofer-Gesellschaft

Citation: Robot speeds up glass development (2011, November 7) retrieved 23 June 2024 from <https://phys.org/news/2011-11-robot-glass.html>

This document is subject to copyright. Apart from any fair dealing for the purpose of private study or research, no part may be reproduced without the written permission. The content is provided for information purposes only.